



Start-up & Shut Down Procedures: Track-Type Tractors – Coal Applications

SAFETY.CAT.COMTM

Operator/Inspector _____ Date _____ Time _____
 Serial Number _____ Machine Hours _____

Was procedure step completed properly?	✓	Evaluator Comments
For more information, please refer to the Operation and Maintenance Manual or any other applicable manuals and instructions for this product. If you have questions, please contact your local Caterpillar dealer.		

STARTING THE MACHINE...

Perform walk around inspection		
Mount the machine using 3 points of contact		
Turn the battery disconnect switch to ON		
Engage the parking brake.		
Adjust seat, fasten seat belt.		
Make sure all implements are grounded.		
Move transmission control lever into neutral.		
Move the attachment control levers into HOLD.		
Make sure all personnel are clear of machine.		
Set the throttle control to LOW IDLE.		
Turn the key start switch to ON		
Perform start-up test on EMS or CMS		
Turn the key start switch to START. Crank engine.		

MACHINE WARM-UP...

Allow machine to warm-up for 5 minutes at low idle.		
Engage and disengage attachment controls to help speed warm-up of hydraulic components.		
Cycle all controls to allow warm oil to circulate through all cylinders and lines.		
Check gauges and action lights frequently.		
If the machine has an EMS, perform second part of start-up test.		

MOVING THE MACHINE...

Make sure area is clear.		
Raise all lowered implements.		
Depress brake pedal.		
Release parking brake.		
Move transmission control to desired direction.		
Release brake pedal and check for proper operation.		

MACHINE SHUT DOWN...

Park machine on smooth, level area.		
Set the parking brake.		
Lower all hydraulic implements.		
Move throttle control to LOW IDLE and run 5 minutes.		
Turn key start switch to OFF and remove key.		
Turn battery disconnect switch to OFF		
Dismount machine using 3-point contact.		
Conduct post-operation walkaround inspection.		

[HTTP://SAFETY.CAT.COM/CHECKLISTS](http://SAFETY.CAT.COM/CHECKLISTS)

V0611.2